



## Product Information

### Description du produit:

There are 2 types of beam expander: fixed and adjustable beam expanders. For the fixed beam expanders, the spacing between the two lenses inside the beam expander is fixed, but the spacing between the two lenses inside the adjustable beam expanders is adjustable.

Carmanhaas [Fixed Magnification Beam Expanders Manufacturer](#) the lens material is ZeSe, which allows the red light to go through the beam expander.

Carmanhaas could offer 3 types of beam expanders: Fixed Beam Expanders, Zoom Beam Expanders and Adjustable divergence angle beam expanders at various wavelengths of 355nm, 532nm, 1030-1090nm, 9.3um, 10.6um.

Other wavelengths and custom-designed beam expanders are available upon request. ([Variable Zoom Laser Beam Expanders Supplier](#)) For more information, please feel free to contact us.


**CARMAN HAAS**

### CO<sub>2</sub> Beam Expander

Improve the collimation of the beam,  
Change the size and characteristics  
of the beam divergence.







**Paramètres techniques:**

Part number Description: BE-XXX-DYY : ZZZ-BB-A

BE ----- Beam Expanders

XXX -----Laser wavelength: 10.6 means 10.6um, 10600nm, CO2

DYY : ZZZ -----Beam Expander Output CA : Housing Length

BB ----- Rapport d'expansion (grossissement) en temps

A ----- AFFRESSIONS DE DIVERGENCE DE DIVERGENCE RÉGLABLES DE BAISON D'ANGLE;

Aucun signifie expandeur de faisceau fixe.

## Dégénérateurs de faisceau de CO2 (10.6UM)

Part Description	Expansion Ratio	Input CA (mm)	Output CA (mm)	Housing Dia(mm)	Housing Length (mm)	Mounting Thread
BE-10.6-D17:46.5-2X	2X	12.7	17	25	46.5	M22*0.75
BE-10.6-D20:59.7-2.5X	2.5X	12.7	20	25	59.7	M22*0.75
BE-10.6-D17:64.5-3X	3X	12.7	17	25	64.5	M22*0.75
BE-10.6-D32:53-3.5X	3.5X	12.0	32	36	53.0	M22*0.75
BE-10.6-D17:70.5-4X	4X	12.7	17	25	70.5	M22*0.75
BE-10.6-D20:72-5X	5X	12.7	20	25	72.0	M30*1
BE-10.6-D27:75.8-6X	6X	12.7	27	32	75.8	M22*0.75
BE-10.6-D27:71-8X	8X	12.7	27	32	71.0	M22*0.75



Factory







重要仪器,  
非专业人士勿动。

OptiCentric 300

TRIOPTICS







PerkinElmer Lambda 950---Testing Transmission and Reflectivity







# CERTIFICATE

## ATTESTATION CERTIFICATE OF MACHINERY AND LOW VOLTAGE DIRECTIVES

Technical file of the company mentioned below has been observed and audit has been completed successfully. 2006/42/EC Machinery Directive and 2014/35/EU Low Voltage Directive have been taken as references for these processes

Company Name : **Camnan HAAS Laser Technology (Suzhou) Co., Ltd.**

Company Address : No 155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Jiangsu , P.R.China

Related Directives and Annex : **Low Voltage Directive 2014/35/EU  
Machinery Directive 2006/42/EC**

Related Standards : **EN ISO 12100:2010; EN 60204-1:2006+A1:2009+AC:2010**

Product Name : **Laser Marking Machine**

Report No and Date : SD-90049717:09.08.2018

Product Brand/Model/Type : LMCH-3W,LMCH-5W,LMCH-10W,LMCH-15W,LMCH-20W,LMCH-25W,  
LMCH-30W,LMCH-50W,LMCH-60W,LMCH-70W,LMCH-100W,  
LMCH-120W,LMCH-150W,LMCH-200W,LMCH-300W,LMCH-500W

Certificate Number : **M.2018.201.N6073**

Initial Assessment Date : 10.08.2018

Registration Date : 13.08.2018

Reissue Date/No :

Expiry Date : **12.08.2023**

*U. Bayraktar*  
UDEM International Certification  
Auditing Training Centre Industry  
and Trade Inc. Co.

The validity of the certificate can be checked through [www.udem.com.tr](http://www.udem.com.tr). The CE mark shown on the right can only be used under the responsibility of the manufacturer with the completion of EC Declaration of Conformity for all the relevant Directives. This certificate remains the property of UDEM International Certification Auditing Training Centre Industry and Trade Inc. Co. to whom it must be returned upon request. The above named firm must keep a copy of this certificate for 15 years from the registration of certificate. This certificate only covers the product(s) stated above and UDEM must be notified in case of any changes on the product(s)  
Address: Mulkikent Mahallesi 2073 Sokak (Eski 93 Sokak) No:10 Çankaya - Ankara - TÜRKİYE  
Phone: +90 0312 443 03 90 Fax: +90 0312 443 03 70  
E-mail: info@udemtd.com.tr www.udem.com.tr



## Certificate of Approval

Certificate No.: 10119Q12565ROM

Awarded to

**Carman Haas Laser Technology(SuZhou)  
Co., Ltd.**

Organization Code Certificate No. / Unified Social Credit Code:91320594MA1MF4EP56  
Add.:No.155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Jiangsu Province, P.R. China. 215000

Beijing ZhongLian TianRun Certification Center (ZLTR) certify that the  
Quality Management System of the above organization has been assessed and found to be  
in accordance with the requirements of the standard:  
**GB/T19001-2016 / ISO9001:2015**

SCOPE OF CERTIFICATION/REGISTRATION  
The Research and Development and Production of Optics Lenses (Except the limits of  
national laws and regulations.)

This certificate is made valid when used with certification scopes and the requirements of applicable  
laws and regulations. These requirements include, but are not limited to, administrative permits,  
scopes of qualifications, and CCC requirements.

Subject to operation conditions in requirements conformity with Quality Management System,

This Certificate is valid for a period of three years only,  
Date from: **Mar 13th,2019 To: Mar 12th,2022**

The effectiveness of this Certificate shall be Validated by periodic surveillance audit  
of ZLTR for maintenance.  
Information of this certificate can be found on the official website of Beijing Zhonglian Tianrun  
Certification center (<http://www.zltr.com.cn>)



Beijing Zhongliantianrun Certification Center

Room2603, 22nd Floor, 2nd Unit, Block 1, No.4 Yard, Qiyang Road, Chaoyang District, Beijing, P.R. China 100102

Information of this certificate can be found on the official website of Certification and Accreditation Administration of the People's Republic of China (<http://www.cnca.gov.cn>)


ISO 9001

ISO 9001



## Packing List





**Politique de retour:**

Devrait revenir être requis:

Étape 1) Contactez-nous avec ce site Web Email.

L'étape 2) fournit le plus de détails possible sur le problème que vous rencontrez.

Étape 3) L'autorisation de renvoyer l'article sera émise.

Étape 4) Remettez l'article pour le remplacement ou le remboursement convenus.

### **Logistique:**

(1) Pour l'ordre de l'optique laser, expédier par DHL, UPS, FedEx, TNT, EMS, etc.

(2) Pour l'ordre de la machine laser, peut être facultatif avec des termes d'EXW, FOB, CNF, CIF par avion ou par voie maritime sur la base de la transitaire de l'acheteur ou de la nôtre.



## FAQ

Q1. Êtes-vous un fabricant?

A1: Oui, nous sommes fabricants professionnels et expérimentés avec nos propres moules et lignes de production.

Q2. Comment la qualité des produits?

A2: Nos techniciens et équipes de QC testent les produits un par un à l'aide de la ligne de vieillissement, des appareils professionnels et des instruments pour assurer la qualité de tous les produits.

Q3. Comment le prix?

A3: Nous sommes un fabricant et nous offrons toujours à nos clients les prix les plus compétitifs.

Q4. Comment passer une commande?

A4: Contact avec le service en ligne ou envoyé par courrier électronique directement par courrier électronique, nous vous répondrons avec le prix du produit, les spécifications, l'emballage, etc. bientôt. Merci.

Q5. May j'envoie du matériel pour tester les performances de marquage?

A5: Oui! Vous êtes invité à envoyer des documents pour tester notre qualité et notre service supérieur.

Q6. Can je visite votre usine?

A6: Oui, bienvenue pour visiter notre usine à votre temps commode.

Q7. Comment-je faire des commandes OEM ou ODM?

A7: Nous avons un traitement d'impression différent pour différents orders OEM / ODMers. S'il vous plaît contactez-nous avec un service en ligne ou envoyez-nous un e-mail directement.

Q8. Comment devrais-je payer mes commandes?

A8: Vous pouvez payer par T / T serait disponible pour une banque qualifiée et un MOQ requis pour chaque commande.