

Carmanhaas

Carmanhaas

Carmanhaas is a breed of dog that is known for its intelligence and loyalty. It is a medium-sized breed that is often used as a working dog. Carmanhaas dogs are known for their ability to learn quickly and their strong bond with their owners. They are also known for their ability to work in a variety of environments, from farms to urban areas. Carmanhaas dogs are a popular choice for people who are looking for a loyal and intelligent companion.

Carmanhaas dogs are known for their intelligence and loyalty. They are a medium-sized breed that is often used as a working dog. Carmanhaas dogs are known for their ability to learn quickly and their strong bond with their owners. They are also known for their ability to work in a variety of environments, from farms to urban areas. Carmanhaas dogs are a popular choice for people who are looking for a loyal and intelligent companion.

Carmanhaas dogs are known for their intelligence and loyalty. They are a medium-sized breed that is often used as a working dog. Carmanhaas dogs are known for their ability to learn quickly and their strong bond with their owners. They are also known for their ability to work in a variety of environments, from farms to urban areas. Carmanhaas dogs are a popular choice for people who are looking for a loyal and intelligent companion.

Si Reflector Mirror

Gold coating, silicon material

Gold coating, silicon material



Detail Image



□□□□□ □□□□□:

□□□□ □□□□	□□□□□
□□□□ □□□□□□□□	0.000 "/ -0.005"
□□□□ □□□□□□□□	± 0.010 "
□□□□□□□□□□□: (Plano)	≤ 3 □□□□ □□□□
□□□ □□□□□□ (□□□□□)	□□□□□ □□ 90%
□□□□□□□□□ @ 0.63um	□□□□: 2 □□□□□□□, □□□□□□□□□: 1 □□□□□□□
□□□□□-□□□□	10-5

□□□□□□□ □□□□□□□□:

□□□□□ (□□□□□)	□□□□ (□□□□□)	□□□□
19/20	3	□□□□□□ / UC@10.6 □□ ATFR / UC@10.6um
25 / 25.4	3	
28	8	
30	3/4	
38.1	3/4/8	
44.45	9.525	
50.8	5 / 5.1	
50.8	9.525	
76.2	6.35	

□□□□□□□ □□□□ □□□□:

□□□□□ (□□□□□)	□□□□ (□□□□□)	□□□□
25	3	RPR -90 / UC@10.6
30	3/4	
50.8	9.525	
76.2	6.35	




🏠 Advantage

- High purity, low absorption material (body absorption less than 0.0005/cm-1)
- High damage threshold coating (>8000W/cm2)
- Lens focusing reaches diffraction limit

Laser light path schematic

① Laser tube ② First mirror ③ Second mirror ④ Third mirror ⑤ Focus lens



□□□□ □□ **30mm** □□□□ **3mm** □□□□ □□□□ □□ □□□□□□□□ □□□□ □□□□ □□ □□ □□







重要仪器,
非专业人士勿动。

OptiCentric 300

TRIOPTICS






PerkinElmer Lambda 950---Testing Transmission and Reflectivity







□□□□ □□□:

□□□□□ □□□□□ □□□ □□□□□:

- 1) □□ □□□□□□ □□□□ □□ □□□ □□□□ □□□□□
- 2) □□□□□□ □□ □□ □□□ □□ □□□□ □□ □□□ □□ □□□ □□□□□ □□□□□□ □□ □□□ □□□ □□□□□ □□□□□
- 3) □□□□□□□□□ □□□□□□ □□□□ □□□□ □□ □□□□□□
- 4) □□□□□ □□□□□□□□□□□ □□ □□□□□ □□ □□□ □□□□□□□

□□□:

□□□□ □□□□□□□□ □□□□□, □□□□□□□, □□□□□□□, FedEx, □□□□□□□, □□□□□□ □□□ □□□□□□ □□□□ □□ □□□

□□□□ □□□□ □□□□ □□ □□□□, □□□□□□ □□□ □□ □□ □□□□□□ □□□□□□□□ □□ □□□□□ □□□□ □□ □□□□□□ □□ Exwork, □□□□□□, CNF, □□□□□□ □□ □□□□□□ □□ □□□ □□□□□□□□ □□ □□□□ □□□

□□□□□□□ □□□□□□□

□□ □□ □□□□□□□□ Q1.Are?

A1: □□□, □□ □□□□ □□ □□ □□□□□ □□ □□□□□□ □□□□□□ □□ □□□ □□□□□ □□ □□□□□ □□□□□□ □□□□□

□□□□□□□□ □□ □□□□□□□ □□ □□□□ □□□ Q2.How?

□□ 2: □□□□□□ □□□□□□□□□□ □□ QC □□□□□□, □□□□□ □□□□□ □□□□ □□ □□□□□ □□□□□□□ □□ □□□□□□ □□□ □□□□□□□□ □□ □□□□□□ □□□□□□□□ □□□□ □□ □□-□□ □□□□ □□□□□□□□ □□ □□□□□□□□

□□□□ □□ □□□□ □□□ Q3.How?

□□ 3: □□ □□ □□□□□□□□ □□□ □□ □□□□□ □□□□ □□□□□□□□ □□ □□□□ □□□□□□□□□□□□ □□□□□□ □□□□□ □□□□ □□□□

Q4.How □□□ □□□□ □□□□ □□ □□□?

□□ 4: □□□□□□ □□□□□, □□ □□□□ □□□□ □□□□ □□ □□□ □□□□□□□, □□ □□□□ □□□□□□ □□ □□□□, □□□□□□□□□□ □□ □□□ □□□ □□□□ □□ □□□□□ □□□□□ □□□□□, □□□□□□□□□□

Q5.May □□□ □□□□□□□ □□□□ □□□□□□□ □□□□ □□ □□□ □□□□□□□ □□□□□?

A5: □□□! □□ □□□□□ □□□□□ □□□□□□□□ □□ □□□□ □□ □□□□□ □□□□ □□ □□□ □□□□□ □□□□ □□ □□□ □□□□□ □□□

Q6.Can □□□ □□□□ □□□□□□□ □□ □□□□?

□□ 6: □□□, □□□□ □□□□□□□□□ □□□ □□ □□□□□ □□□□□□□ □□ □□□□ □□□□ □□ □□□□□ □□□□ □□□□

Q7.How □□□ OEM □□ ODM □□□□ □□ □□□□ □□□?

□□ 7: □□ □□□□□□□ □□□ □□ □□□□□□ □□□□□□□□□□ □□ / ODM ord□□□□□□□ □□□□□□ □□□□□ □□□□ □□ □□□ □□□□ □□□□□

□□□□□□ □□□ □□□ □□□□ □□ □□□ □□□□□ □□□□ □□□□□□?

□□ 8: □□ □□ □□□□□□ □□□□□□ □□ □□□□ □□□□ □□ □□□□□ □□□□ □□ □□□ □□□□□ □□□□ □□ □□□ □□□□□ □□□□ □□□□ □□□□ □□□□