Product Description

QBH Optical Modul Supplier China Carmanhaas offer professional laser optical system with galvo scan laser processing. The entire system is a separate functional module that enables plug-and-play functionality. Processing by galvanometer scanning, mainly include: QBH collimation module / beam expander, galvanometer system, F-theta scan lens, in which QBH collimation module / beam expander realizes shaping of light source (diverging parallel or small spot becomes large spot), the galvanometer system realizes beam.

Advantage:


- (1) Material is Fused silica;
- (2) High damage threshold coating (damage threshold: 40 J/cm2, 10 ns);

Coating absorption <20 ppm. Ensure that the scan lens can be saturated at 8KW;


- (3)Optimized index design, collimation system wavefront $< \lambda/10$, ensuring diffraction limit;
- (4)Optimized for heat dissipation and cooling structure, ensuring no water cooling below 1KW, temperature <50°C when using 6KW;
- (5) With a non-thermal design, the focus drift is <0.5mm at 80 °C;
- (6)Complete range of specifications, customers can be customized.



Welding F theta Lenses Factory China







Technical Parameters:


1030-1090nm F-Theta Lenses

Part Description	Focal Length (mm)	Scan Field (mm)	Max Entrance Pupil (mm)	Working Distance(mm)	Mounting Thread
SL-1064-100-170-(14CA)	170	100x100	14	215	M79x1/M102x1
SL-(1030-1090)-150-210-(15CA)	210	150x150	15	269	M79x1/M102x1
SL-(1030-1090)-175-254-(15CA)	254	175x175	15	317	M79x1/M102x1
SL-(1030-1090)-90-175-(20CA)	175	90x90	20	233	M85x1
SL-(1030-1090)-160-260-(20CA)	260	160x160	20	333	M85x1
SL-(1030-1090)-100-254-(30CA)-M102*1-WC	254	100x100	30	333	M102x1/M85x1
SL-(1030-1090)-180-348-(30CA)-M102*1-WC	348	180x180	30	438	M102x1
SL-(1030-1090)-180-400-(30CA)-M102*1-WC	400	180x180	30	501	M102x1
SL-(1030-1090)-250-500-(30CA)-M112*1-WC	500	250x250	30	607	M112x1/M100x1

QBH Collimation Module

Part Description	Focal Length (mm)	Clear Aperture (mm)	Max NA	Coating
CL2-(900-1100)-30-F60-QBH-A-WC	60	28	0.22	AR/AR@1030-1090nm
CL2-(900-1100)-30-F100-QBH-A-WC	100	28	0.13	AR/AR@1030-1090nm
CL2-(900-1100)-30-F125-QBH-A-WC	125	28	0.10	AR/AR@1030-1090nm
CL2-(900-1100)-38-F100-QBH-A-WC	100	34	0.16	AR/AR@1030-1090nm
CL2-(900-1100)-38-F125-QBH-A-WC	125	34	0.13	AR/AR@1030-1090nm
CL2-(900-1100)-38-F135-QBH-A-WC	135	34	0.12	AR/AR@1030-1090nm
CL2-(900-1100)-38-F150-QBH-A-WC	150	34	0.11	AR/AR@1030-1090nm
CL2-(900-1100)-38-F200-QBH-A-WC	200	34	0.08	AR/AR@1030-1090nm





白车身 Body-in-White



Sun gear, Ring gear Viscous damper Synchronization ring





Differential gear Planetary carrier





Flywheel









Recliner

Backrest

Seat Frame




Factory









PerkinElmer Lambda 950---Testing Transmission and Reflectivity



CERTIFICA

ATTESTATION CERTIFICATE OF MACHINERY AND LOW VOLTAGE DIRECTIVES

Technical file of the company mentioned below has been observed and audit has be completed successfully, 2006/42/EC Machinery Directive and 2014/ 35/EU Low Voltage Directive have been taken as references for these proces

: No 155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Company Address Jiangsu , P.R.China

Related Directives and Annex : Low Voltage Directive 2014/35/EU Machinery Directive 2006/42/EC

Related Standards : EN BO 12100:2010; EN 60204-1:2006+A1:2009+AC:2010

Report No and Date : SD-90049717;09.08.2018

Product Brand/Model/Type : LMCH-3W,LMCH-5W,LMCH-10W,LMCH-15W,LMCH-20W,LMCH-25W,

LMCH-30W,LMCH-50W,LMCH-60W,LMCH-70W,LMCH-100W, LMCH-120W,LMCH-150W,LMCH-200W,LMCH-300W,LMCH-500W


Certificate Number Initial Assessment Date : M.2018.201.N6073 : 10.08.2018 UDEA International C Registration Date : 13.08.2018 Reissue Date/No

and Trade Inc. Co

Address: Mutakent Mahallesi 2073 Sokak (Ekki 93 Sokak) No:10 Çankaya – Ankara – TURKEY Phone: +90 0312 443 03 90 Fax: +90 0312 443 03 76 E-mak kin0-udenith.com.tr. www.udem.com.tr.



UDEM



Certificate No.: 10119Q12565ROM

Awarded to

Carman Haas Laser Technology(SuZhou) Co., Ltd.

Beijing ZhongLianTianRun Certification Center (ZLTR) certify that the Quality Management System of the above organization has been assessed and found to be in accordance with the requirements of the standard:

GB/T19001-2016 / ISO9001:2015

SCOPE OF CERTIFICATION/REGISTRATION The Research and Development and Production of Optics Lenses (Except the limits of national laws and regulations.)

This certificate is made valid when used with certification scopes and the requirements of applicable laws and regulations. These requirements include, but are not limited to, administrative permits, scopes of qualifications, and CCC requirements.

Subject to operation conditions in requirements conformity with Quality Management System,
This Certificate is valid for a period of three years only,
Date from: Mar 13th,2019 To: Mar 12th,2022

The effectiveness of this Certificate shall be Validated by periodic surveillance audit of ZLTR for maintenance.

Information of this certificate space he loand on the official website of Beijing Zhonglian Tianrun Certificates of the found on the Control of the State of Beijing Zhonglian Tianrun Certificates of the official website of Beijing Zhonglian Tianrun Certification croner (http://www.shr.com.co)



ISO 9001






Beijing Zhongliantianrun Certification Center







Packing List







Return Policy:

Should returns be required:

- Step 1) Contact us with this website email.
- Step 2) Provide as much detail as possible about the problem you are having.
- Step 3) Authorization to return the item will be issued.
- Step 4) Return the item for the agreed replacement or refund.

Logistics:

- (1) For Laser Optics order delivery, can be optional with DHL, UPS, FedEx, TNT, EMS, ets
- (2) For Laser machine order delivery, can be optional with terms of EXWork FOB, CNF, CIF By Air or by Sea based on the buyer's forwarders or ours.

FAO

Q1.Are you a manufacturer?

A1: Yes, we are professional and experienced manufacturer with our own molds and production lines.

Q2. How about quality of products?

A2: Our technicians and QC teams test the products one by one using aging line, professional devices and instruments to ensure the quality for all products.

Q3.How about price?

A3: We are a manufacturer and always offer our customers the most competitive prices.

Q4. How to place an order?

A4: Contact with online service, or sent email to us directly, we will reply to you with product price, specifications, packing etc. soon. Thank you.

Q5.May I send material to test marking performance?

A5: Yes! You are welcome to send material to test our superior quality and service.

Q6.Can I visit your factory?

A6: Yes, welcome to visit our factory at your convenient time.

Q7. How can I make OEM or ODM orders?

A7: We have different print processing for different OEM/ODM orders. Please contact us with online service or send email to us directly.

Q8. How should I pay for my orders?

A8: You can pay by T/T would be available for qualified bank and MOQ required for each order.