## **Product Information**

#### **Product Description:**

(cutting lens factory) Carmanhaas Fiber cutting optical components are used in various types of fiber laser cutting head, transmitting and focusing the beam output from the fiber to achieve the purpose of cutting the sheet.

#### **Product Features:**

- (1)Imported ultra low absorption quartz material
- (2)Surface accuracy:  $\lambda/5$
- (3)Power usage: Up to 15000W
- (4)Ultra-low absorption coating, absorption rate <20ppm, long life time
- (5)Aspherical surface finish accuracy up to 0.2μm







## Focusing lenses supplier

### **Manufacturing Capabilities:**

| Specifications                         |                |  |
|--|----------------|--|
| Substrate Material                     | Fused Silica   |  |
| Dimensional Tolerance                  | +0.000"-0.005" |  |
| Thickness Tolerance                    | ±0.01"         |  |
| Sphere Power                           | 3 fringes      |  |
| Sphere Irregularity                    | 1 fringe       |  |
| Surface Quality                        | 10-5           |  |
| Clear Aperture (polished)              | ≥90 %          |  |
| Effective Focal Length (EFL) Tolerance | < 1.0%         |  |

### **Coating Capabilities:**


| Specifications                            |         |  |  |
|---|---------|--|--|
| Standard Both Sides AR coating @1070nm    |         |  |  |
| Total absorption                          | < 30PPM |  |  |
| Transmittance                             | >99.9%  |  |  |
| Ultra Low-absorbing AR/AR coating @1070nm |         |  |  |
| Total absorption                          | < 10PPM |  |  |
| Transmittance                             | >99.9%  |  |  |

## **Fused Silica Collimating Lens:**

| 25.4 | 75  | AR/AR @ 1030-1090nm |
|------|-----|---------------------|
| 25.4 | 100 | AR/AR @ 1030-1090nm |
| 28   | 75  | AR/AR @ 1030-1090nm |
| 28   | 100 | AR/AR @ 1030-1090nm |
| 30   | 75  | AR/AR @ 1030-1090nm |
| 30   | 100 | AR/AR @ 1030-1090nm |
| 37   | 100 | AR/AR @ 1030-1090nm |

## **Fused Silica Collimating Lens:**

| Diameter(mm) | Focal Length(mm) | Coating             |
|--------------|------------------|---------------------|
| 25.4         | 125              | AR/AR @ 1030-1090nm |
| 28           | 125              | AR/AR @ 1030-1090nm |
| 30           | 125              | AR/AR @ 1030-1090nm |
| 30           | 150              | AR/AR @ 1030-1090nm |
| 30           | 200              | AR/AR @ 1030-1090nm |
| 37           | 150              | AR/AR @ 1030-1090nm |
| 37           | 200              | AR/AR @ 1030-1090nm |
| 38.1         | 300              | AR/AR @ 1030-1090nm |



# **Factory**










TRIOPTICS OptiSpheric 2000 AF
---Testing EFL、R、Centering Error、Wedge Angle、BFL、MTF



PerkinElmer Lambda 950---Testing Transmission and Reflectivity



Carmanhaas Coating Machine

# Certificate&Exhibition









# **Packing List**

## Packaging & Shipping

## Packaging 1









Packaging 2









Packaging 3









Shipping 4



















### **Return Policy:**

Should returns be required:

- Step 1) Contact us with this website email.
- Step 2) Provide as much detail as possible about the problem you are having.
- Step 3) Authorization to return the item will be issued.
- Step 4) Return the item for the agreed replacement or refund.

#### **Logistics:**

- (1) For Laser Optics order delivery, can be optional with DHL, UPS, FedEx, TNT, EMS etc
- (2)For Laser machine order delivery, can be optional with terms of EXWork, FOB, CNF, CIF By Air or by Sea based on the buyer's forwar ders or ours.

### **FAQ**

- Q1.Are you a manufacturer?
- A1: Yes, we are professional and experienced manufacturer with our own molds and production lines.
- Q2. How about quality of products?
- A2: Our technicians and QC teams test the products one by one using aging line, professional devices and instruments to ensure the quality for all products.
- Q3. How about price?
- A3: We are a manufacturer and always offer our customers the most competitive prices.
- Q4. How to place an order?
- A4: Contact with online service, or sent email to us directly, we will reply to you with product price, specifications, packing etc. soon. Thank you.
- Q5.May I send material to test marking performance?
- A5: Yes! You are welcome to send material to test our superior quality and service.
- Q6.Can I visit your factory?
- A6: Yes, welcome to visit our factory at your convenient time.
- Q7. How can I make OEM or ODM orders?
- A7: We have different print processing for different OEM/ODM orders. Please contact us with online service or send email to us directly.
- Q8. How should I pay for my orders?
- A8: You can pay by T/T would be available for qualified bank and MOQ required for each order.