




Описание товара:

SLA (стереолитография) - это добавочный процесс производства, который работает, сосредоточив ультрафиолетовый лазер на НДС фотополимерной смолы. Благодаря справочной программной программное обеспечение для производства компьютеров или компьютеров (CAM / CAD), УФ-лазер используется для рисования предварительно запрограммированного дизайна или формы на поверхность фотополимера НДС. Фотополимеры чувствительны к ультрафиолетовому свету, поэтому смола фотохимически затвердевала и образует один слой желаемого 3D-объекта. Этот процесс повторяется для каждого слоя конструкции, пока 3D-объект не будет завершен.

Carmanhaas может предложить клиенту оптическую систему в основном включает в себя быстрый гальванометр сканера и объектив сканирования F-Theta, расширитель луча, зеркало и т. Д. [355 гальво сканер цена Китай](#) Несомненно





Технические параметры:

355NM Galvo сканер головы

Model	PSH14-H	PSH20-H	PSH30-H
Water cool/sealed scan head	yes	yes	yes
Aperture (mm)	14	20	30
Effective Scan Angle	±10°	±10°	±10°
Tracking Error	0.19 ms	0.28ms	0.45ms
Step Response Time(1% of full scale)	≤ 0.4 ms	≤ 0.6 ms	≤ 0.9 ms
Typical Speed			
Positioning / jump	< 15 m/s	< 12 m/s	< 9 m/s
Line scanning/raster scanning	< 10 m/s	< 7 m/s	< 4 m/s
Typical vector scanning	< 4 m/s	< 3 m/s	< 2 m/s
Good Writing quality	700 cps	450 cps	260 cps
High writing quality	550 cps	320 cps	180 cps
Precision			
Linearity	99.9%	99.9%	99.9%
Resolution	≤ 1 urad	≤ 1 urad	≤ 1 urad
Repeatability	≤ 2 urad	≤ 2 urad	≤ 2 urad
Temperature Drift			
Offset Drift	≤ 3 urad/°C	≤ 3 urad/°C	≤ 3 urad/°C
Over 8hours Long-Term Offset Drift (After 15min warn-up)	≤ 30 urad	≤ 30 urad	≤ 30 urad
Operating Temperature Range	25°C±10°C	25°C±10°C	25°C±10°C
Signal Interface	Analog: ±10V Digital: XY2-100 protocol	Analog: ±10V Digital: XY2-100 protocol	Analog: ±10V Digital: XY2-100 protocol
Input Power Requirement (DC)	±15V@ 4A Max RMS	±15V@ 4A Max RMS	±15V@ 4A Max RMS

355nm F-тета линзы

Part Description	Focal Length (mm)	Scan Field (mm)	Max Entrance Pupil (mm)	Working Distance(mm)	Mounting Thread
SL-355-360-580	580	360x360	16	660	M85x1
SL-355-520-750	750	520x520	10	824.4	M85x1
SL-355-610-840-(15CA)	840	610x610	15	910	M85x1
SL-355-800-1090-(18CA)	1090	800x800	18	1193	M85x1

355NM Expander

Part Description	Expansion Ratio	Input CA (mm)	Output CA (mm)	Housing Dia(mm)	Housing Length(mm)	Mounting Thread
BE3-355-D30:84.5-3x-A(M30*1-M43*0.5)	3X	10	33	46	84.5	M30*1-M43*0.5
BE3-355-D33:84.5-5x-A(M30*1-M43*0.5)	5X	10	33	46	84.5	M30*1-M43*0.5
BE3-355-D33:80.3-7x-A(M30*1-M43*0.5)	7X	10	33	46	80.3	M30*1-M43*0.5
BE3-355-D30:90-8x-A(M30*1-M43*0.5)	8X	10	33	46	90.0	M30*1-M43*0.5
BE3-355-D30:72-10x-A(M30*1-M43*0.5)	10X	10	33	46	72.0	M30*1-M43*0.5


355 нмЗеркало

ЧастьОписание	ДиаметрЭтер (мм)	Толщина (мм)	Покрытие
355.Зеркало	30.	3.	HR @ 355 нм, 45 ° AOI
355.Зеркало	20.	5.	HR @ 355 нм, 45 °Ава
355.Зеркало	30.	5.	HR @ 355 нм, 45 °Ава


[УФ-F-Theta Lens Производитель Китай](#)



PHYSICAL CHARACTERISTICS (LIQUID STATE)	Appearance: White liquid Density: 1.10 g/cm ³ @25°C Viscosity: 450 CPS @25°C Dp: ≥0.16 mm Ec: 8.5 mJ/cm ²
	MOLDING PERFORMANCE A MOLDING PERFORMANCE @355nm point laser @330mW power @5.0m/s scanning @No UV post-cure Bending Modulus: 1500~1700 MPa Bending Strength: 55~60 MPa Notched Impact Strength: 60~68 J/m 1.2mm Bend Angle: 140~170°
MOLDING PERFORMANCE B MOLDING PERFORMANCE @90min UV post-cure Bending Modulus: 2688~2790 MPa Bending Strength: 66~73 MPa Notched Impact Strength: 60~68 J/m Hardness: 88 Elongation at break: 10~15% HDT Heat deflection temperature: 52 °C Tg Glass transition temperature: 62 °C CTE Coefficient of thermal expansion: 93°E-6	



PHYSICAL CHARACTERISTICS (LIQUID STATE)	Appearance: White liquid Density: 1.10 g/cm ³ @25°C Viscosity: 400 CPS @25°C Dp: ≥0.16 mm Ec: 7.9 mJ/cm ²
	MOLDING PERFORMANCE A MOLDING PERFORMANCE @355nm point laser @330mW power @5.0m/s scanning @No UV post-cure Bending Modulus: 2000~2300 MPa Bending Strength: 75~85 MPa Notched Impact Strength: 35~45 J/m 1.2mm Bend Angle: ≥170~180°
MOLDING PERFORMANCE B MOLDING PERFORMANCE @90min UV post-cure Bending Modulus: 2813~3520 MPa Bending Strength: 83~90 MPa Notched Impact Strength: 42~50 J/m Hardness: 87~92 Elongation at break: 13~20% HDT Heat deflection temperature: 52 °C Tg Glass transition temperature: 62 °C CTE Coefficient of thermal expansion: 93°E-6	



<p>PHYSICAL CHARACTERISTICS (LIQUID STATE)</p>	<p>Appearance: Transparent liquid Pale Purple</p> <p>Density: 1.10 g/cm³ @25°C</p> <p>Viscosity: 190 CPS @25°C</p> <p>Dp: ≥0.18 mm</p> <p>Ec: 6.9 mJ/cm²</p>
<p>MOLDING PERFORMANCE A</p> <p>MOLDING PERFORMANCE</p> <p>@355nm point laser</p> <p>@150mW power</p> <p>@5.0m/s scanning</p> <p>@No UV post-cure</p>	<p>Appearance: High Transparency</p> <p>Transmittance: 85% (MAX)</p> <p>Bending Modulus: 1500~1700 MPa</p> <p>Bending Strength: 45~55 MPa</p> <p>Notched Impact Strength: 25~35 J/m</p> <p>1.2mm Bend Angle: 140~170°</p>
<p>MOLDING PERFORMANCE B</p> <p>MOLDING PERFORMANCE</p> <p>@90min UV post-cure</p>	<p>Bending Modulus: 1890~2340 MPa</p> <p>Bending Strength: 55~62 MPa</p> <p>Notched Impact Strength: 40~55 J/m</p> <p>Hardness: 79</p> <p>Elongation at break: 10~15%</p> <p>HDT Heat deflection temperature: 52 °C</p> <p>Tg Glass transition temperature: 62 °C</p> <p>CTE Coefficient of thermal expansion: 93*E-6</p>

Real ABS (ABS Like)



<p>PHYSICAL CHARACTERISTICS (LIQUID STATE)</p>	<p>Appearance: Bright yellow liquid</p> <p>Density: 1.10 g/cm³ @25°C</p> <p>Viscosity: 400 CPS @25°C</p> <p>Dp: ≥0.16 mm</p> <p>Ec: 7.9 mJ/cm²</p>
<p>MOLDING PERFORMANCE A</p> <p>MOLDING PERFORMANCE</p> <p>@355nm point laser</p> <p>@330mW power</p> <p>@5.0m/s scanning</p> <p>@No UV post-cure</p>	<p>Bending Modulus: 2000~2300 MPa</p> <p>Bending Strength: 75~85 MPa</p> <p>Notched Impact Strength: 35~45 J/m</p> <p>1.2mm Bend Angle: ≥170~180°</p>
<p>MOLDING PERFORMANCE B</p> <p>MOLDING PERFORMANCE</p> <p>@90min UV post-cure</p>	<p>Bending Modulus: 2813~3520 MPa</p> <p>Bending Strength: 83~90 MPa</p> <p>Notched Impact Strength: 42~50 J/m</p> <p>Hardness: 87~92</p> <p>Elongation at break: 13~20%</p> <p>HDT Heat deflection temperature: 52 °C</p> <p>Tg Glass transition temperature: 62 °C</p> <p>CTE Coefficient of thermal expansion: 93*E-6</p>

Red Wood (Tooling Board Like)



<p>PHYSICAL CHARACTERISTICS (LIQUID STATE)</p>	<p>Appearance: Epoxy Tooling Board Like (Pink) liquid Density: 1.10 g/cm³ @25°C Viscosity: 400 CPS @25°C Dp: ≥0.16 mm Ec: 7.9 mJ/cm²</p>
<p>MOLDING PERFORMANCE A MOLDING PERFORMANCE @355nm point laser @330mW power @5.0m/s scanning @No UV post-cure</p>	<p>Bending Modulus: 2000~2300 MPa Bending Strength: 75~85 MPa Notched Impact Strength: 35~45 J/m 1.2mm Bend Angle: ≥170~180°</p>
<p>MOLDING PERFORMANCE B MOLDING PERFORMANCE @90min UV post-cure</p>	<p>Bending Modulus: 2813~3520 MPa Bending Strength: 83~90 MPa Notched Impact Strength: 42~50 J/m Hardness: 87~92 Elongation at break: 13~20% HDT Heat deflection temperature: 52 °C Tg Glass transition temperature: 62 °C CTE Coefficient of thermal expansion: 93*E-6</p>




Desktop FDM

Industrial FDM

Desktop SLA

Industrial SLA

Industrial SLS





Factory







重要仪器,
非专业人士勿动.

OptiCentric 300

TRIOPTICS





PerkinElmer Lambda 950---Testing Transmission and Reflectivity







C E R T I F I C A T E

ATTESTATION CERTIFICATE OF MACHINERY AND LOW VOLTAGE DIRECTIVES

Technical file of the company mentioned below has been observed and audit has been completed successfully. 2006/42/EC Machinery Directive and 2014/35/EU Low Voltage Directive have been taken as references for these processes

Company Name : **Camnan HAAS Laser Technology (Suzhou) Co., Ltd.**

Company Address : No 155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Jiangsu , P.R.China

Related Directives and Annex : **Low Voltage Directive 2014/35/EU
Machinery Directive 2006/42/EC**

Related Standards : **EN ISO 12100:2010; EN 60204-1:2006+A1:2009+AC:2010**

Product Name : **Laser Marking Machine**

Report No and Date : SD-90049717:09.08.2018

Product Brand/Model/Type : LMCH-3W,LMCH-5W,LMCH-10W,LMCH-15W,LMCH-20W,LMCH-25W,
LMCH-30W,LMCH-50W,LMCH-60W,LMCH-70W,LMCH-100W,
LMCH-120W,LMCH-150W,LMCH-200W,LMCH-300W,LMCH-500W

Certificate Number : **M.2018.201.N6073**

Initial Assessment Date : 10.08.2018

Registration Date : 13.08.2018

Reissue Date/No :

Expiry Date : **12.08.2023**

Signature
UDM International Certification
Auditing Training Centre Industry
and Trade Inc. Co.



The validity of the certificate can be checked through www.udem.com.tr. The CE mark shown on the right can only be used under the responsibility of the manufacturer with the completion of EC Declaration of Conformity for all the relevant Directives. This certificate remains the property of UDEM International Certification Auditing Training Centre Industry and Trade Inc. Co. to whom it must be returned upon request. The above named firm must keep a copy of this certificate for 15 years from the registration of certificate. This certificate only covers the product(s) stated above and UDEM must be notified in case of any changes on the product(s)
Address: Mulkikent Mahallesi 2073 Sokak (Eski 93 Sokak) No:10 Çankaya - Ankara - TÜRKİYE
Phone: +90 0312 443 03 90 Fax: +90 0312 443 03 70
E-mail: info@udemtd.com.tr www.udem.com.tr



Certificate of Approval

Certificate No.: 10119Q12565ROM

Awarded to

**Carman Haas Laser Technology(SuZhou)
Co., Ltd.**

Organization Code Certificate No. / Unified Social Credit Code:91320594M1MF4EP56
Add.:No.155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Jiangsu Province, P.R. China. 215000

Beijing ZhongLian TianRun Certification Center (ZLTR) certify that the
Quality Management System of the above organization has been assessed and found to be
in accordance with the requirements of the standard:
GB/T19001-2016 / ISO9001:2015

SCOPE OF CERTIFICATION/REGISTRATION

The Research and Development and Production of Optics Lenses (Except the limits of national laws and regulations.)

This certificate is made valid when used with certification scopes and the requirements of applicable laws and regulations. These requirements include, but are not limited to, administrative permits, scopes of qualifications, and CCC requirements.

Subject to operation conditions in requirements conformity with Quality Management System,

This Certificate is valid for a period of three years only,

Date from: Mar 13th,2019 To: Mar 12th,2022

The effectiveness of this Certificate shall be Validated by periodic surveillance audit of ZLTR for maintenance.

Information of this certificate can be found on the official website of Beijing Zhonglian Tianrun Certification center (<http://www.zltr.com.cn>)



Beijing Zhongliantianrun Certification Center

Room2603, 22nd Floor, 2nd Unit, Block 1, No.4 Yard, Qiyang Road, Chaoyang District, Beijing, P.R. China 100102

Information of this certificate can be found on the official website of Certification and Accreditation Administration of the People's Republic of China (<http://www.cnca.gov.cn>)

ISO 9001

ISO 9001



Packing List



Политика возврата:

Должна ли потребоваться возврата:

- Шаг 1) Свяжитесь с нами с помощью этого веб-сайта электронной почты.
Шаг 2) Обеспечить как можно больше деталей о проблеме, которую вы имеете.
Шаг 3) Авторизация для возврата товара будет выдано.
Шаг 4) Верните товар на согласованную замену или возмещение.

Логистика:

(1) для лазерной оптики Заказать Доставка, может быть необязательно с DHL, UPS, FedEx, TNT, EMS, ETS

(2) для Лазермашина порядок Доставка, банка быть по желанию с участием термина из Прошлая работа FOB, CNF, CIF К Воздух или Морена основании на то покупатель экспедиторы или наш.



FAQ

Q1. Вы производитель?

A1: Да, мы являемся профессиональным и опытным производителем с нашими собственными формами и производственными линиями.

Q2. Как о качестве продуктов?

A2: Наши специалисты и контрольные команды QC тестируют продукты по одному, используя линию старения, профессиональные устройства и инструменты для обеспечения качества для всех продуктов.

Q3. Как о цене?

A3: Мы являемся производителем и всегда предлагаем нашим клиентам наиболее конкурентоспособные цены.

Q4. Как сделать заказ?

A4: Контакт с онлайн-сервисом или отправляю нам электронное письмо напрямую, мы ответим вам с ценой продукта, спецификациями, упаковкой и т. Д. Спасибо.

Q5. may Я отправляю материал для проверки производительности маркировки?

A5: Да! Вы можете отправить материал для проверки нашего превосходного качества и обслуживания.

Q6. CAN Я посещаю свою фабрику?

A6: Да, добро пожаловать на наш завод в удобное время.

Q7. Как я могу сделать OEM или ODM заказы?

A7: У нас разная обработка печати для разных OEM / ODM ORD. Пожалуйста, свяжитесь с нами с онлайн-сервисом или отправьте нам электронное письмо напрямую.

Q8. Как мне платить за мои заказы?

A8: Вы можете оплатить Т / Т будет доступен для квалифицированного банка и MOQ для каждого заказа.