

## "Описание товара"

**Китай профессиональный производитель круглых защитных окон Znse**Окна Carmanhaas часто используются в оптических системах для отделения окружающей среды в одной части системы от другой, например, для герметизации вакуумных ячеек или ячеек высокого давления. Поскольку материал, передающий инфракрасное излучение, имеет высокий показатель преломления, на окна обычно наносится антибликовое покрытие, чтобы минимизировать потери из-за отражений.

Для защиты линз сканирования от брызг и других опасностей на рабочем месте Carmanhaas предлагает защитные окна, также известные как окна для мусора, которые либо входят в состав всей сборки линзы сканирования, либо продаются отдельно. Эти плоско-плоские окна доступны как из материалов ZnSe, так и из Ge, а также поставляются установленными или несмонтированными.





## "Технические параметры"

Характеристики	Стандарты
Допуск размеров	+0,000 "/ -0,005"
Допуск толщины	± 0,010 "
Параллельность: (Plano)	≤ 3 угловых минут
Clear Aperture (полированная)	90% диаметра
Рисунок поверхности @ 0,63 мкм	Мощность: 1-я, Неровность: 0,5-м.
Scratch-Dig	20-10

## □Окна с покрытием ZnSe AR□

Диаметр (мм)	ET (мм)	Тип покрытия	Длина волны (мкм)
12,7	2,5	AR / AR	10,6
19	2	AR / AR	10,6
20	2/3	AR / AR	10,6
25	2/3	AR / AR	10,6
25,4	2/3	AR / AR	10,6
38,1	1,5 / 3	AR / AR	10,6
70	3	AR / AR	10,6
80	3	AR / AR	10,6
90	3	AR / AR	10,6
100	3	AR / AR	10,6
12Lx12W	1	AR / AR	10,6
135Lx102W	3	AR / AR	10,6
161Lx110W	3	AR / AR	10,6
25 / 25,4	3	AR / AR	9,2-9,7
38,1	3/4	AR / AR	9,2-9,7

**Примечание:** если вам нужны другие характеристики и покрытие, пожалуйста, свяжитесь с нашим отделом продаж. ([лазерная фокусировка производитель линз Китай](#))

## Lens Cleaning

### 1. For light pollution (dust, fiber particles) were flexible cleaning.

Using a blowing balloon, Blow off scattered contaminants on the surface of the optical element.



### 2. For light pollution (stains, fingerprints) were flexible cleaning.

Propanol, acetone glue with a cotton swab or alcohol to gently wipe the surface.




### 3. For moderately polluted (saliva, oil) in moderate-intensity cleaning.

Infiltrating distilled white vinegar with a cotton swab, wipe the surface a little pressure.



☐Выставка и сертификаты☐





# C E R T I F I C A T E

## ATTESTATION CERTIFICATE OF MACHINERY AND LOW VOLTAGE DIRECTIVES

Technical file of the company mentioned below has been observed and audit has been completed successfully. 2006/42/EC Machinery Directive and 2014/ 35/EU Low Voltage Directive have been taken as references for these processes

Company Name : **Camnan HAAS Laser Technology (Suzhou) Co., Ltd.**

Company Address : No 155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Jiangsu , P.R.China

Related Directives and Annex : **Low Voltage Directive 2014/35/EU  
Machinery Directive 2006/42/EC**

Related Standards : **EN ISO 12100:2010; EN 60204-1:2006+A1:2009+AC:2010**

Product Name : **Laser Marking Machine**

Report No and Date : SD-90049717:09.08.2018

Product Brand/Model/Type : LMCH-3W,LMCH-5W,LMCH-10W,LMCH-15W,LMCH-20W,LMCH-25W,  
LMCH-30W,LMCH-50W,LMCH-60W,LMCH-70W,LMCH-100W,  
LMCH-120W,LMCH-150W,LMCH-200W,LMCH-300W,LMCH-500W

Certificate Number : **M.2018.201.N6073**

Initial Assessment Date : 10.08.2018

Registration Date : 13.08.2018

Reissue Date/No :

Expiry Date : **12.08.2023**

*Signature*  
UDM International Certification  
Auditing Training Centre Industry  
and Trade Inc. Co.

The validity of the certificate can be checked through [www.udem.com.tr](http://www.udem.com.tr). The CE mark shown on the right can only be used under the responsibility of the manufacturer with the completion of EC Declaration of Conformity for all the relevant Directives. This certificate remains the property of UDEM International Certification Auditing Training Centre Industry and Trade Inc. Co. to whom it must be returned upon request. The above named firm must keep a copy of this certificate for 15 years from the registration of certificate. This certificate only covers the product(s) stated above and UDEM must be notified in case of any changes on the product(s)  
Address: Mulkikent Mahallesi 2073 Sokak (Eski 93 Sokak) No:10 Çankaya - Ankara - TÜRKİYE  
Phone: +90 0312 443 03 90 Fax: +90 0312 443 03 70  
E-mail: info@udemtd.com.tr www.udem.com.tr



## Certificate of Approval

Certificate No.: 10119Q12565ROM

Awarded to

**Carman Haas Laser Technology(SuZhou)  
Co., Ltd.**

Organization Code Certificate No. / Unified Social Credit Code:91320594MA1MF4EP56  
Add.:No.155, West Road Suhong, Suzhou Industrial Park, Suzhou City, Jiangsu Province, P.R. China. 215000

Beijing ZhongLianTianRun Certification Center (ZLTR) certify that the  
Quality Management System of the above organization has been assessed and found to be  
in accordance with the requirements of the standard:  
**GB/T19001-2016 / ISO9001:2015**

SCOPE OF CERTIFICATION/REGISTRATION

The Research and Development and Production of Optics Lenses (Except the limits of national laws and regulations.)

This certificate is made valid when used with certification scopes and the requirements of applicable laws and regulations. These requirements include, but are not limited to, administrative permits, scopes of qualifications, and CCC requirements.

Subject to operation conditions in requirements conformity with Quality Management System,

This Certificate is valid for a period of three years only,  
Date from: Mar 13th,2019 To: Mar 12th,2022

The effectiveness of this Certificate shall be Validated by periodic surveillance audit  
of ZLTR for maintenance.

Information of this certificate can be found on the official website of Beijing Zhonglian Tianrun  
Certification center (<http://www.zltr.com.cn>)

ISO 9001

ISO 9001



Beijing Zhongliantianrun Certification Center

Room2603, 22nd Floor, 2nd Unit, Block 1, No.4 Yard, Qiayang Road, Chaoyang District, Beijing, P.R. China 100102

Information of this certificate can be found on the official website of Certification and Accreditation Administration of the People's Republic of China (<http://www.cnca.gov.cn>)

## Заводская выставка









重要仪器,  
非专业人士勿动。

OptiCentric 300

TRIOPTICS





PerkinElmer Lambda 950---Testing Transmission and Reflectivity



# "Товарная накладная"

## Packaging & Shipping

### Packaging 1



### Packaging 2




### Packaging 3



### Shipping 4





**Логистика:**

(1) Доставка заказа лазерной оптики может быть опциональной через DHL, UPS, FedEx, TNT, EMS и т. Д.

(2) Доставка заказа на лазерную машину может быть необязательной на условиях EXWork, FOB, CNF, CIF по воздуху или по морю в зависимости от экспедиторов покупателя или наших.

### **Политика возврата:**

Если требуется возврат:

Шаг 1) Свяжитесь с нами по этому адресу электронной почты.

Шаг 2) Предоставьте как можно больше подробностей о проблеме, с которой вы столкнулись.

Шаг 3) Будет выдано разрешение на возврат товара.

Шаг 4) Верните товар для согласованной замены или возврата денег.

## **"ВОПРОСЫ-ОТВЕТЫ:"**

### **Q1.Вы производитель?**

A1: Да, мы профессионалы и опытные [Фокусирующие линзы производитель](#) с собственными формами и производственными линиями.

### **Q2.Как насчет качества продукции?**

A2: Наши технические специалисты и группы контроля качества тестируют продукты один за другим, используя линию старения, профессиональные устройства и инструменты, чтобы гарантировать качество всех продуктов.

### **Q3.Как насчет цены?**

A3: Мы являемся производителем и всегда предлагаем нашим клиентам самые конкурентоспособные цены.

### **Q4.Как разместить заказ?**

A4: Свяжитесь с онлайн-службой или отправьте нам электронное письмо напрямую, мы скоро ответим вам с ценой продукта, спецификациями, упаковкой и т. Д. Спасибо.

### **Q5.Могу ли я отправить материал для проверки качества маркировки?**

A5: Да! Вы можете прислать материалы для проверки нашего превосходного качества и обслуживания.

### **Q6.Могу ли я посетить ваш завод?**

A6: Да, приглашаем вас посетить наш завод в удобное для вас время.

### **Q7.Как я могу сделать заказы OEM или ODM?**

A7: У нас есть различная обработка печати для разных заказов OEM / ODM. Пожалуйста, свяжитесь с нами через онлайн-сервис или отправьте нам электронное письмо напрямую.

### **Q8. Как мне оплачивать заказы?**

A8: Вы можете оплатить T / T, будет доступен для квалифицированного банка и MOQ, необходимый для каждого заказа.