

### 1064nm Beam Expander

| P/N            | Substrate    | Magnification | Dia (mm) | Length (mm) | Input CA (mm) | Output CA (mm) | Connect  |
|----------------|--------------|---------------|----------|-------------|---------------|----------------|----------|
| BEX-2X-1064nm  | Fused Silica | 2             | 27       | 48.5        | 10            | 21.6           | M22*0.75 |
| BEX-3X-1064nm  | Fused Silica | 3             | 27       | 68          | 10            | 21.6           | M22*0.75 |
| BEX-4X-1064nm  | Fused Silica | 4             | 27       | 76          | 10            | 21.6           | M22*0.75 |
| BEX-5X-1064nm  | Fused Silica | 5             | 27       | 72          | 10            | 21.6           | M22*0.75 |
| BEX-6X-1064nm  | Fused Silica | 6             | 27       | 74          | 10            | 21.6           | M22*0.75 |
| BEX-8X-1064nm  | Fused Silica | 8             | 27       | 68          | 10            | 21.6           | M22*0.75 |
| BEX-10X-1064nm | Fused Silica | 10            | 27       | 69.5        | 6             | 21.6           | M22*0.75 |
| BEX-15X-1064nm | Fused Silica | 15            | 27       | 87          | 6             | 21.6           | M22*0.75 |



YAG Beam Expander



YAG Beam Expander

## Trade Shows

2014



2015



2016



## Packaging & Shipping

### Packaging 1



### Packaging 2



### Packaging 3



### Shipping 4



